




WORLDWIDE LEADER OF SOURCE SAMPLING EQUIPMENT

▶ Compact Method 5 Sampling Kit Independently Heated Stainless-Steel Filter Assembly



The compact Method 5 kit does not require a separate heated filter compartment and utilizes a flexible sample line and a split umbilical cord with a power adapter to allow sampling in space-limited areas.

Scan the QR Code for
More Information


Features

- Independently heated stainless steel filter assembly (SFA-82H) that connects directly to a standard Method 5 probe
- Flexible sample line and a split umbilical cord with a power adapter to allow sampling in space-limited areas
- Standard glass impingers have been replaced with stainless steel impingers (SN-5CREVA) to eliminate glass breakage
- Three filter assemblies are recommended to speed up the turnaround time between consecutive runs. All applicable components are rated 120 V at 60 Hz



▶ Compact Method 5 Sampling Kit Part # SK-CM5-□ Packing List

Heated Filter Assembly



Your Method 5 Sampling Solution



SCAN THE QR CODE FOR THE COMPLETE PACKING LIST